



Fast as lightning. Sparkling clean. KR AGILUS Hygienic Machine.

KR AGILUS Hygienic Machine

THE HYGIENE CONCEPT: The robot's design and materials allow it to be used in applications involving direct contact with foodstuffs and pharmaceutical substances. Corrosion-resistant surfaces, food-compatible lubricants and stainless steel parts ensure the highest level of hygiene.


EASY TO CLEAN: Thanks to its hygienic design, deposits cannot form on the surface or screws of the six-axis robot. The cleaning-sensitive electrical interface is not located in the primary contact area but rather underneath the robot. Cleaning is possible using industry-standard cleaning agents as well as high pressure.



2	KR 6 R900 sixx HM-SC	KR 10 R900 sixx HM-SC
Max. reach ———	901.5 mm	901.5 mm
Max. payload ———	——————————————————————————————————————	10 kg
Pose repeatability —	±0.03 mm	±0.03 mm
Number of axes ——	6	б
Mounting position —		—— Floor, ceiling, wall
Weight (excluding con	troller), approx. — 62 kg	————— 62 kg

The interface plate underneath the KR AGILUS HM-SC

- **1** Resolver input for axis 7
- 2 Resolver input for axis 8
- **3** Pneumatic connections (Air 1, Air 2, compressed air)
- 4 Extension Interface (100 MBit)
- 5 Motor connector
- 6 Interface connection



KUKA Roboter GmbH

Zugspitzstraße 140, 86165 Augsburg, Germany, Phone: +49 821 797-4000, www.kuka-robotics.com

Details provided about the properties and usability of the products are purely for information purposes and do not constitute a guarantee of these characteristics. The extent of goods delivered and services performed is determined by the subject matter of the specific contract. No liability accepted for errors or omissions.

Axis data Range of motion

Axis 1 (A1)	+/-166°	
Axis 2 (A2)		+45°/-188°
Axis 3 (A3)		+144°/-115°
Axis 4 (A4)	+/-185°	
Axis 5 (A5)	+/-110°	+/-110°
Axis 6 (A6)		

Operating conditions

Ambient temperature, robot	 +0 °C to +	40 °C

Protection rating

Protection rating, robot -

— IP 67

Controller

- KR C4 compact KR C4 smallsize-2

Teach pendant

KUKA smartPAD

